

DRAWING NO
P8797

3RD ANGLE PROJECTION

REMOVE ALL SHARP EDGES AND BURRS




FINISH:- Hi Phos Electroless Nickel plate to BS EN ISO 4527:2003

| ENTRY SIZE | MIN SHELL SIZE | F DIA MIN | G | H |
|---|---|---|---|---|
| 03 | 09 | 4,45 | - | - |
| 04 | 09 | 6,35 | - | - |
| 05 | 09 | 7,92 | - | - |
| 06 | 09 | 9,53 | - | - |
| 07 | 09 | - | 9,7 | 11,8 |
| 08 | 15 | - | 9,7 | 17,9 |
| 09 | 25 | | 9,7 | 25,0 |
| 10 | 25 | - | 9,7 | 32,0 |

| SHELL SIZE | A | B | C +0.2/-0 | D | E |
|---|---|---|---|---|---|
| 09 | 31.00 | 25.0 | 11.7 | 12.2 | 12.93 |
| 15 | 39.20 | 33.3 | 11.7 | 12.2 | 12.93 |
| 25 | 53.00 | 47.0 | 11.7 | 12.2 | 12.93 |
| 37 | 69.50 | 63.5 | 11.7 | 12.2 | 12.93 |
| 50 | 66.90 | 61.1 | 14.5 | 15.2 | 15.75 |

100P2475-09-04-L40-CHP

- SERIES
- SHELL SIZE
- ENTRY SIZE
- LENGTH IN MM
- FINISH

| ISSUE | DCR NO. | DATE | APPROVED |
|---|---|---|---|
| 1 | 2234 | 06/06/2007 | MXF |
| | | | |
| | | | |
| | | | |
| | | | |

MATERIAL

ALUM ALLOY 6082-T6

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS IN MILLIMETRES
TOLERANCE ON DIMENSIONS +/-0.1MM
TOLERANCE ON ANGLES +/- 1 DEGREE

WEIGHT

DRAWN M.PAUL

DO NOT SCALE THIS DRAWING

THIS DRAWING IS COPYRIGHT, AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.

POLAMCO LTD
WESTON LOCK
LOWER BRISTOL ROAD
BATH BA2 1EP

PART NO 100P2475-09-04-L40B

TITLE

D SUB BANDING ADAPTOR

ASSY USED ON
MIL-C-24308

DRAWING NO
P8797

Downloaded from Arrow.com.