



4 MARKED 'AMP', PART NO. & DATE CODE
THIS APPROXIMATE AREA.

5 ACTION PIN POSTS REQUIRE .093 MIN
THK PC BOARD. RECOMMENDED PC BOARD
HOLES ARE .0453 DIA DRILL PLATED
THROUGH WITH .001-.003 COPPER, WITH
.0003 MIN TIN-LEAD PLATING. FINISHED
HOLE AFTER PLATING, .037-.043 DIA.



THIS DRAWING IS A CONTROLLED DOCUMENT.										 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: R K SEIFERD 1/10/86 CHK: G STEINHAUER 1/11/86		NAME: _____ PIN HEADER ASSEMBLY, HDI SERIES-100 HYBRID, 3-ROW, SQUARE PORTS		SIZE: _____ CASE CODE: _____ DRAWING NO: _____ A1 00779 C=533429		RESTRICTED TO: _____ _____	
INCHES				APVD: G STEINHAUER 1/11/86							
		0 P.L.C. ± - 1 P.L.C. ± - 2 P.L.C. ± - 3 P.L.C. ± .005 4 P.L.C. ± - ± - ANGLES FINISH		PRODUCT SPEC: _____ APPLICATION SPEC: _____							
MATERIAL		 		WEIGHT: 0							
				CUSTOMER DRAWING		SCALE: 4:1		SHEET 1 OF 1		REV: N	