



Products

Customize Your
Parts

Industries
Solutions

Search

News &
Events

First
Time?



Home / Products / X-Lok / Mini Size

Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- GGI >



AD-05BFFM-QL8D01

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: PVC
- Certificate: UL2238, UL50e

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok. Accessory...
AB-AD-000505-0FM-...
-20°C ~ +85°C

X-Lok. Accessory...
AB-AD-050505-FFM-...
-20°C ~ +85°C

X-Lok. Accessory...
AB-AD-050505-FMF-...
-20°C ~ +85°C

X-Lok. Accessory...
AB-AD-050505-MFM-...
-20°C ~ +85°C

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 5A	Connector Type Overmolded
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender Female	Backshell Straight
Mating Style Push Lock	IP Rating IPX8
Assembly Style N/A	
<div><div></div> More Options</div>	

People Also Bought

