Part Number : 640010700
Product Description : Hand Crimp Tool
Series Number : 207129
Status : Obsolete
Product Category : Crimp Presses and Crimp Hand Tools
Engineering Part Number : RHT-5757-CC



Obsolete

Documents and Resources

Tooling Specifications

ATS-640010700-001.pdf
TM-640160065-001.pdf
TM-640160065CN-001.pdf
TM-640160065DE-001.pdf
TM-640160065SP-001.pdf
TM-640160065FR-001.pdf
TM-640160065IT-001.pdf
TM-640160065JP-001.pdf
TM-640160065KR-001.pdf
TM-640160065MY-001.pdf
TM-640160065PL-001.pdf
TM-640160065RU-001.pdf
TM-640160065SK-001.pdf
TM-640160065TH-001.pdf
TM-640160065VN-001.pdf
TM-640160065TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active

Downloaded from Arrow.com.

Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054598818
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized

Obsolete

Downloaded from Arrow.com.

	distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Tab 6.35 x 0.81mm, Salmon, Carton	190030001
InsulKrimp Quick Disconnect, Female, Box, Tab 6.35 x 0.81mm, Carton	190030005
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Box, Tab 6.35 x 0.81mm, Carton	190030008
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Tab 4.75 x 0.51mm, Salmon, Carton	190030011
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Box, Tab 4.75 x 0.51mm, Carton	190030014
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Tab 4.75 x 0.81mm, Pink, Carton	190030017
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Box, Tab 4.75 x 0.81mm, Carton	190030021
InsulKrimp Quick Disconnect,	190030024

Obsolete

Downloaded from Arrow.com.

Female, for 18-22 (0.80-0.35mm^2), Tab 2.79 x 0.51mm, Salmon, Carton	
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Tab 2.79 x 0.81mm, Pink, Carton	190030030
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Tab 5.21 x 0.51mm, Salmon, Carton	190030036
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2), Tab 5.21 x 0.81mm, Pink, Carton	190030038
Perma-Seal Female Quick Disconnect for 22-18 AWG Wire, Tab Size 6.35 x 0.81mm, Carton	191640012
Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Red, 22-18 AWG, Loose, Carton	192760002

Obsolete

Downloaded from Arrow.com.