



Part Number : [1301430129](#)

Product Description : Watertite Extreme Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-20 125V

Series Number : 130143

Status : Active

Product Category : Wiring Devices

Engineering Number : 14W33D123



Documents & Resources

Drawings

[1301430129 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Not Relevant

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Watertite Extreme Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-20 125V
IP Rating	IP67
NEMA Configuration	NEMA 5-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678871009

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	30.48m (100.0')
Lighted Connector	No

Locking Blade	No
Net Weight	999.000/g
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on Sep 24, 2025