
Part Number : RM672-252-322-9000
Product Description : AirBorn R Series, Rectangular Board Mount Plug, Right-Angle, Plastic Body, 6 Rows, 0.075"/1.91mm Pitch, with Mounting Ears, Through Hole, 0.140" Tail Length, Full Round Guide Pins Installed, Pre-Tinned Tin/Lead Alloy Termination, 252 Circuits
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Symbol and Footprint (Multi-Format)

Specifications

Materials Specification - R Series

Performance Specification

PC Board Layout (Sizes 162 to 402)

Hardware Polarization (4 & 6 Row)

Contacts (6 Row)

Dimensional Information

Part Number Buildup

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Description	AirBorn R Series, Rectangular Board Mount Plug, Right-Angle, Plastic Body, 6 Rows, 0.075"/1.91mm Pitch, with Mounting Ears, Through Hole, 0.140" Tail Length, Full Round Guide Pins Installed, Pre-Tinned Tin/Lead Alloy Termination, 252 Circuits
Application	Board-to-Board, Wire-to-Board
Comments	Through Hole

Downloaded from Arrow.com.

Component Type	Plug
Contact Type	Pin
Product Name	AirBorn R Series
Series	R Series

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	750V

Physical

Breakaway	No
Circuits (Loaded)	252
Circuits (maximum)	252
Color - Resin	Gray
Durability (mating cycles max)	500
Glow-Wire Capable	No
Guide to Mating Part	Full Round Guide Pins - Installed
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Beryllium Copper, Brass Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Pre-Tinned Tin/Lead Alloy
Material - Shell	Polyphenylene Sulfide
Number of Rows	6
Orientation	Right Angle
Packaging Type	Carton
PCB Retention	Yes
PC Tail Length	0.140"
Pitch - Mating Interface	0.075" (1.91mm)
Pitch - Termination Interface	0.075" (1.91mm)
Plating min - Mating	50µ”
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-65° to +125°C
Termination Interface Style	Through Hole

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description
Rectangular, Plastic, 6 Row, Solder Cup Cable Mount Receptacle
Rectangular, Plastic, 6 Row, Vertical Board Mount Receptacle
Rectangular, Plastic, 6 Row, Right Angle Board Mount Receptacle
Rectangular, Plastic, 6 Row, Vertical Press-Fit Receptacle

Downloaded from Arrow.com.