

Series D xx S 24B 6 xx 12 LF

Number of contacts
09 , 15 , 25

Contacts
S : Socket

Plating
6 = 500 Mating / Unmating Mini

Packaging specification
Tape & Reel

See Note RoHS

Termination

Code	Type	Foot Print/Pitch	Length of termination	PCB thickness
24B	Straight version	6 / 2.84mm	2.90	2.4

Mounting Options

RL	Insert M3
RV	Female Screw UNC 4-40
RX	Insert UNC 4-40

NOTE RoHS iNFORMATION

- The "LF" product meet european union Directives and other country regulations asdescribed in GS-22-008.
- The housing will whistand exposure to 260° peak temperature for 30 seconds in a convection , infra-red or vapor reflow oven. See application notes/procedures if are available.
- Termination plating spec:1.27µ Nickel mini,2.5 to 7.5µ Sn(pure mate)
- Shell plating : Nickel bright
- Accessories : Sn pure bright
- Packaging spec ; See GS-14-920



Product Specification




see : GS-12-372

Packaging Specification


See GS-14-1054

ltr	ecn no	dr	date
I	CREATED	HLE	06/08/24
A	LS06-0223	PCR	2006/12/21
B	110-0120	NG	2010-05-27
C	110-0197	NG	2010-10-14
-	-	-	-
-	-	-	-
-	-	-	-



www.fciconnect.com			surface -  ISO 1302		tolerance std ISO 406 ISO 1101		projection 					
TOLERANCES UNLESS OTHERWISE SPECIFIED												
Dr	P. CRON	02/02/06	ANGULAR		LINEAR		0.X	±0.3	size A3	Scale 3:1		
Eng	H. LEGALLIC	02/02/06					0.XX	±0.1				
Chr	NIRMAL G	2010-10-14					0.XXX	±0.05				
Appr	SUDHIR V	2010-10-14	0°	±2°	Product family			-	Spec ref -			
			title SUB DELTA D PIP FEMALE H=2 straight for tape and reel packaging				dwg. no C01-8646-0886				Rev. C	
			catalog no SEE TABLE				customer			sheet 1 of 2		



SECTION C-C SEE DETAIL A




PCB Card Drilling dimensions and Pads recommended
(after plating - Thickness : 240 mm)




DETAIL A
SCALE 10:1

TRUE POSITIONING : $\oplus \varnothing 0.36$


Accessories details



TYPE RX / RL



TYPE RV



SHELL	P/N LEAD FREE	A ±0.38	B ±0.10	C ±0.10	D +0.25 0	F	G
09	D09S24B6xx12LF	30.81	24.99	16.96	16.21	10.96	8.22
15	D15S24B6xx12LF	39.14	33.32	25.18	24.54	19.18	16.44
25	D25S24B6xx12LF	53.03	47.04	39.12	38.25	33.12	30.36

www.fciconnect.com		surface - ☒ ISO 1302	tolerance std ISO 406	projection ISO 1101	mm	
		TOLERANCES UNLESS OTHERWISE SPECIFIED		$\oplus \ominus$		
Dr	P. CRON	02/02/06	ANGULAR	LINEAR	0.X	±0.3
Eng	H. LEGALLIC	02/02/06			0.XX	±0.1
Chr	NIRMAL G	2010-10-14	0° ±2°		0.XXX	±0.05
Appr	SUDHIR V	2010-10-14	Product family		- Spec ref	
title		SUB DELTA D PIP FEMALE H=2.54		size	A2	
straight for tape and reel packaging		C01-8646-0886		Scale	3:1	
catalog no		SEE TABLE		customer		sheet 2 of 2