

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/23/19	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:**Material:**

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contacts : Copper Alloy, Tin plated

Electrical:

Voltage rating: 600 V

Current rating: 27 A

Dielectric withstanding voltage: 2,200 V for 1 minute

Mechanical:

Wire range: 10~24AWG

Wire strip length: 15-16mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 01 thru 24

A= .295 [7.50] x No. of Positions + .047 [1.20]

B= .295 [7.50] x No. of Space

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN

OW

9/23/19

CHECKED

EY

9/23/19

APPROVED

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

.295 [7.50] PITCH SPRING CLAMP
TERMINAL BLOCKS, RIGHT ANGLE

SIZE

X

PART NO.

EB171SA-XX-M

REV.

-

REF:

S00067C

SCALE:

NTS

SHEET 1 OF 1

6

5

4

3

2

1