

# Female insert 20A, blue



Image is for illustration purposes only. Please refer to product description.

Part number	11 05 105 2815
Specification	Female insert 20A, blue
HARTING eCatalogue	<a href="https://harting.com/11051052815">https://harting.com/11051052815</a>

## Identification

Category	Inserts
Series	Han-Yellock®
Element	Multiplier
Specification	5 Bridged contacts 0 Unbridged contacts

## Version

Gender	Female
Number of contacts	5

## Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	$\geq 500$

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 5015 (sky blue)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

## Commercial data

Packaging size	2
Net weight	6.06 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140109728
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522