



REV

ECO

DESCRIPTION

DATE

BY

APPR

B1

-

RELEASE NEW DWG FORMAT

Jun.16,2014

Tod

Tommy

B2

-

UPDATE THE PART NUMBER

Jun.27,2015

Drack

Tommy

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

BODY: ZINC DIE CAST, NICKEL PLATED

BOOT: TPE(BLACK)

2. SPECIFICATIONS:

2.1 DEGREE OF PROTECTION: IP67 (MATED CONDITION)

MUST BE POTTED TO ACHIEVE IP67 RATING

2.2 RoHS COMPLIANT

3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

		Cable OD Range
1	MB4FSR-B10.3	9.5~10.3 mm
2	MB4FSR-B12.5	11.5~12.5 mm
3	MB4FSR-B14.5	13.5~14.5 mm
4	MB4FSR-B17.0	15.5~17.0 mm

SEE PART NUMBER

CHART

QUANTITY

PART NUMBER

DESCRIPTION

ITEM

UNLESS OTHERWISE SPECIFIED

1) All dimensions are in metric(mm).

2) Tolerances are as follows:

1 PL DEC ±0.30

2 PL DEC ±0.15

3 PL DEC ±0.08

3) Note reference = 

SIGNATURES

DRAWN: Drack

CHECKED:

ENGINEER:

APPROVAL:

CUSTOMER:

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

DATE

Jun.27,2015

Amphenol

Sine Systems - www.amphenol-sine.com

44724 Morley Drive

Clinton Township, MI 48036

M23B,Flexible Strain Relief

SIZE

B

TYPE

C-

DWG NO:

MB4FSR-Bxxx

REVISION

B2

SCALE:

NONE

SHEET

1

OF

1

TITLE:

M23B,Flexible Strain Relief

DWG NO:

MB4FSR-Bxxx

REV:

B2

SH:

1

OF:

1

Downloaded from [Arrow.com](#)