



Part Number : 1301030025

Series Number : 130103

Product Category : Lamps and Lights

Product Description : Watertite Wet Location Incandescent Hand Lamp, 100W with Clear Poly Carbonate Globe, Screw Release Grounded Vinyl Guard, Cord Type 16/3 SOOW, Cord Length 15.24m (50.0')

Status : New Business Not Supported

Engineering Number : 1203IB163P

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Lamps and Lights

Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with Clear Poly Carbonate Globe, Screw Release Grounded Vinyl Guard, Cord Type 16/3 SOOW, Cord Length 15.24m (50.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Family	Hand Lamps
Product Name	Watertite
Type	Hand Lamps
UPC	78678838710

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Grounded, Insulated, Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Clear Polycarbonate

Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on May 04, 2024