

Search This Product Catalogue

By Keyword

Go

- Maintenance and Repair (MRO) Solutions
- Product Catalogue for Maintenance and Repair (MRO) Solutions
- Abrasives

Adhesives

Aerosols

Cleaning

Electrical Products

Fastening

Matting

Safety

Tapes

Product Catalogue for Maintenance and Repair (MRO) Solutions>Electrical Products>3M™ Lugs and Connectors>3M™ Scotchlok™ Copper Connectors>3M™ Scotchlok™ 10000 Series Copper Connectors>

3M™ Scotchlok™ Copper Standard Barrel Connector 10006, up to 35 kV, 2/0 AWG, Black

Printer-friendly format



click to enlarge

This connector is a Black, 2/0 AWG with a length of 2 in (50,8 mm), and a 0.439 in (11,2 mm) I.D.

3M Order Code : 80-6100-3302-1
Bar Code : 0 00 54007 12774 1

Additional Information

The 3M™ Scotchlok™ Copper Standard Barrel Connector 10006 is used on copper conductors only. It is constructed of one-piece, seamless, high-conductivity copper. This connector is a Black, 2/0 AWG with a length of 2 in (50,8 mm), and a 0.439 in (11,2 mm) I.D.

Learn More . . .

Packaging Data

- Email3M Scotchlok 10000 Series Copper Connector-Standard-Barrel -35kV - Product Selection Guide (PDF 7.7 K)
- Email3M Scotchlok 11000 Series Copper Connector-Long-Barrel to 35kV - Product Selection Guide (PDF 5.8 K)
- Email3M™ Lugs and Connectors, 2013 Electrical Products Catalog - Catalog (PDF 2.1 MB)
- Email3M™ Scotchlok™ Copper Compression Connectors, 10000/11000 - Data Sheet (PDF 42.3 K)

Please Note:
Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Agency Approvals	UL LISTED
Barrel Style	Standard Barrel
Color Code	Black
For Use With	Copper Conductor Only
Inside Diameter	0.44 Inch
Inside Diameter (metric)	11.2 mm
Length	2 Inch
Length (metric)	50.8 Millimetre
Maximum Voltage	35 Kilovolt
Outside Diameter	0.56 Inch
Outside Diameter (metric)	14.2 mm
RoHS 2011/65/EU Compliant	Yes