




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWING	26AUG21	S.T	I.Y
	A1	REVISE	21JUL22	C.C	Z.Z



SECTION A-A



- 1 MATERIAL: PA66-GF30
COLOR: SEE TABLE
2. BULK PACKAGED

A1

2394113-3	CABLE COVER - 70SQ	1	ORANGE	Ø 17.4	16.7	17.3
2394113-2	CABLE COVER - 50SQ	1	ORANGE	Ø 15.3	14.6	15.2
2394113-1	CABLE COVER - 35SQ	1	ORANGE	Ø 13.1	12.4	13.0
PART NO.	DESCRIPTION	MATERIAL	COLOR	DIM.A	MIN.	MAX.
					CABLE O.D.	


DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±0.3

0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±

DWN
S.TAN

26AUG2021

CHK
J.LI

26AUG2021

APVD
I.YIN

26AUG2021

PRODUCT SPEC

108-160341

APPLICATION SPEC

114-160182

WEIGHT

MATERIAL

1

FINISH

TE

TE Connectivity

NAME

CABLE COVER
HVP-HD1000

SIZE

A 4

CAGE CODE

00779

DRAWING NO

C-2394113

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

1:1

SHEET

1 OF 1

REV

A1