



Part Number : [1300250290](#)

Product Description : Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, Gray DeviceNet Thin (Drop) Cable, 2.0m (6.56') Length

Series Number : 130025

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : DND11A-M020




Documents and Resources

Drawings

[1300250290_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead... per D(2024)4144-DC (27 June 2024) SCIP:cce17fdc-b58a-4314-bb3e-5c1a23018e94 |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 130025 |
| Description | Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, Gray DeviceNet Thin (Drop) Cable, 2.0m (6.56') Length |
| IP Rating | IP67 |
| Product Name | DeviceNet Trunk,Mini-Change |
| Type | Double Ended |
| UPC | 78678801095 |

Agency

| | |
|-----|---------|
| CSA | LR6837 |
| UL | E152210 |

Electrical

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 300V AC/DC |

Physical

| | |
|----------------|----------------|
| Cable Diameter | 7.24mm (.285") |
| Cable Length | 2.0m (6.56') |

| | |
|-------------------------------|----------------------|
| Color - Cable Jacket | Gray |
| Connector End A | Mini-Change |
| Connector End B | Mini-Change |
| Coupling Style | Threaded |
| Gender | Female-Male |
| Keyway | Single |
| LED Indicator | None |
| Material - Cable Jacket | PVC |
| Material - Connector Body | TPE |
| Material - Contact | Brass |
| Material - Coupling Nut | Zinc Die-Cast |
| Material - Plating Mating | Gold |
| Net Weight | 220.921/g |
| Orientation | Straight to Straight |
| Poles | 5 |
| Temperature Range - Operating | -20° to +80°C |
| Wire/Cable Type | Thin (Drop) |
| Wire Size (AWG) | 22 |

This document was generated on May 15, 2026