



**Catalog No. TY34M**

**Description:** CABLE TIE 40LB 6IN NAT NYL MTG HOLE

**UPC No** 786210824864

**Home > Wire & Cable Management > Ty-Rap > Mounted Head Ties**

Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 152mm (6 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 177 Newtons (40 pounds), #8 Screw for Mounting, Bulk Pack

**Descriptors**

Category	Mounted Head Ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

**Specifications**

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds , 180 newtons

**Classifications**

Brand Name	Ty-Rap
Standard	UL E49405

**Dimensions**

Width	0.14 in , 3.6 mm
Length	6 in , 152 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.08 to 1.14 in , 2 to 29 mm

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	3.6 mm
Length belt/tape/tie	152 mm
Length belt/tape/tie	6 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	29 mm
Min. holding force	177 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
Type of fastening	Screw hole
VG approval	N
MIL approval	N
UL approval	N