

USB-C to RS232 (DB9) Serial Adapter Cable (M/M), 5 ft. (1.52 m)

MODEL NUMBER: U209-005-C



Connect a device with a 9-pin RS-232 serial port to the USB Type-C port on your computer, laptop, tablet or smartphone. Perfect for connecting modems, digital cameras, PDAs and ISDN terminals.

Features

Connects a DB9 Device to a USB-C Device

- Ideal for connecting a modem, digital camera, PDA or ISDN terminal to your computer, laptop, tablet or smartphone
- Supports data transfer speeds up to 230 Kbps—twice as fast as a built-in serial port
- No external power source required
- Portable 5 ft. design fits perfectly into laptop bag

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors with gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces

Broad Compatibility

- Compatible with Windows, Mac, Linux and Android devices (see System Requirements for details)

Specifications

OVERVIEW	
UPC Code	037332197573
Technology	Serial; USB
Host Connector	USB C (MALE)

Highlights

- Supports data transfer speeds up to 230 Kbps
- Premium foil and braid shielding reduces EMI/RFI interference
- Compatible with Windows®, Mac®, Linux® and Android™ devices
- No external power source required
- Portable 5 ft. design fits perfectly into laptop bag

System Requirements

- Windows 2000 and later (including Windows 11)
- Mac OS X 10.6 through 10.12
- Linux Redhat 7.3 through 9.0 (Linux Kernel 2.4.31 and above include built-in drivers)
- Android devices with USB Host Mode (OTG) support and OS 3.2 and later. USB Host Mode (OTG) cable required.

Package Includes

- U209-005-C USB-C to DB9 Serial Adapter Cable (M/M), 5 ft.
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DB9 (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	5
Cable Length (m)	1.52
Shipping Dimensions (hwd / in.)	1.22 x 4.40 x 4.60
Shipping Dimensions (hwd / cm)	3.10 x 11.18 x 11.68
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.