







DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS	DATE
1 BODY	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.3-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN	G.R.S.	04/29/99
2 INSULATOR	TEFLON	NATURAL		CHECKED		
3 BARREL	BRASS	GOLD		ISSUED		
4 CONTACT PIN	BER. COPPER	GOLD				
5 FERRULE	COPPER	GOLD				
6						
7						
8			DO NOT SCALE DRAWING			

TITLE				MMCX CRIMP JACK	
(FOR RG-316/u DOUBLE BRAID CABLE)					
SIZE	FSOAL NO.	DWG. NO.			
A	99001	262119.DWG			
SCALE	NA	PART NO.	262119	SHEET	1 OF 1



Connector Corporation

connex
Connector Corporation

MMCX CRIMP JACK
(FOR RG-316/u DOUBLE BRAID CABLE)