Part Number : 2079118420
Product Description : High-Speed FAKRA Mini (HFM) Quad Jack Housing, 2x2, Key A, Black, with CPA
Series Number : 207911
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2079118420_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2079110012-000.pdf

2088700000PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	207911
Description	High-Speed FAKRA Mini (HFM) Quad Jack Housing, 2x2, Key A, Black, with CPA
Application	Automotive, RF, Wire-to-Wire, Wire-to-Board
Component Type	Housing
Product Name	High-Speed FAKRA Mini (HFM)
UPC	195842780491

Physical

Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	25
Gender	Female
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1.894/g
Number of Rows	2
Packaging Type	Bag

Downloaded from Arrow.com.

Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarization	A
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
High-Speed FAKRA Mini (HFM) Quad Plug Housing, 2x2, Key A, Black, with Clipslot	2079125420
High-Speed FAKRA Mini (HFM) Quad Header, 2x2, Right-Angle, Through Hole, Key A, Black, 50 Ohms	2082440200

Use with Part(s)

Description	Part Number
High-Speed FAKRA Mini (HFM) Jack Inner Contact, for RTK031 Coaxial Cable, Gold (Au) Plating	2079112000
High-Speed FAKRA Mini (HFM) Jack Outer Contact, for RTK031 Coaxial Cable, Tin (Sn) Plating	2079113000
High-Speed FAKRA Mini (HFM) Jack Inner Contact, for RG174 Coaxial Cable, Gold (Au) Plating	2079112001
High-Speed FAKRA Mini (HFM) Jack Outer Contact, for RG174 Coaxial Cable, Tin (Sn) Plating	2079113001
High-Speed FAKRA Mini (HFM) Crimp Sleeve, for RTK031 Coaxial Cable, Tin (Sn) Plating	2079113402
High-Speed FAKRA Mini (HFM) Crimp Sleeve, for RG174 Coaxial Cable, Tin (Sn) Plating	2079113401

Downloaded from Arrow.com.

Downloaded from Arrow.com.