

High Capacity Force Gauge with PC Interface

220lbs (100kg), Tension and Compression

Reading on display reverse direction depending on measurement mode

Features:

- Ranges: 0.05 to 100kg
0.05 to 220lbs
0.2 to 980 Newton
- Basic accuracy of 0.5%
- Tension or Compression, Peak hold and Zero functions
- Positive/Reverse display for easy readability
- Large LCD with back light feature
- Complete with tension and compression adaptors, six AA 1.5V batteries, and case



Complete with tension and compression adaptors, six AA 1.5V batteries, and case

Ordering Information:

475055Force Gauge
475055-NISTForce Gauge with Calibration Traceable to NIST

