

Part Number : [357254110](#)

Product Description : 6.35mm Tab Slip-On Wire-to-Board Terminal, Female, 20+20, 18+18 AWG, Post-Tin Plated

Series Number : 35725

Status : Not Recommended For New Design

Product Category : Crimp Terminals

Documents and Resources

Specifications

[PS-35153-001-001.pdf](#)

[PS-35153-002-001.pdf](#)


[PS-35153-003-001.pdf](#)

[PS-35179-001-001.pdf](#)

[PS-35179-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Crimp Terminals
Series	35725
Description	6.35mm Tab Slip-On Wire-to-Board Terminal, Female, 20+20, 18+18 AWG, Post-Tin Plated
Application	Power
Product Name	N/A
UPC	800754378024

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.706/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Wire Insulation Diameter	2.55mm max.
Wire Size (AWG)	18+18, 20+20
Wire Size mm ²	N/A