

Specification Sheet

Part Number: 133-03405



Can be easily assembled to convoluted tubing and reliably remain in position

Internal rib prevents movement or rattling

Multiple configurations to mount to a variety of surfaces

Releaseable to allow for maintenance

Conduit Clamps, Size 13, Mounting Hole 8.8 mm, PA66, Black, 800/carton

Article Number 133-03405

Type CDC13R40.5M8

Color Black (BK)

Quantity Per carton

Product Description The Convoluted Tubing Clamp provides a quick method for securing and routing convoluted tubing. The clamp has an internal rib that prevents movement of the tubing and rattling. Living hinge allows placement and positioning of tubing before locking in place. Convoluted tubing clamps are available in various tubing diameters.

Short Description Conduit Clamps, Size 13, Mounting Hole 8.8 mm, PA66, Black, 800/carton

Global Part Name	CDC13R40.5M8-PA66-BK
------------------	----------------------

Length L (Imperial)	3.25
---------------------	------

Length L (Metric)	82.5
-------------------	------

Offset Length (Imperial)	1.59
--------------------------	------

Offset Length (Metric)	40.5
------------------------	------

Fixation Method	screwable
-----------------	-----------

Width W (Imperial)	0.9
--------------------	-----

Width W (Metric)	23
------------------	----

Bundle Diameter Max (Imperial)	0.51
--------------------------------	------

Bundle Diameter Max (Metric)	13.0
------------------------------	------

Height H (Imperial)	0.87
---------------------	------

Height H (Metric)	22
-------------------	----

Diameter D (Imperial)	0.55
-----------------------	------

Diameter D (Metric)	14.0
---------------------	------

Mounting Hole Diameter D (Imperial)	0.35
-------------------------------------	------

Mounting Hole Diameter D (Metric)	8.8 mm
-----------------------------------	--------

Stud Diameter (Metric)	M8
Stud Diameter (Imperial)	M8
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	800
Package Quantity (Metric)	800
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)