



C2G
Discontinued - 13.1ft (4m) LC-LC 50/125 OM2 Duplex Multimode Fiber Optic Cable (TAA Compliant) - Orange
Part No. 11033



Cost-effective solution that provides higher bandwidth and transmission rates and supports longer distances with lower loss than 62.5/125 fiber. Specifically designed for use with today's narrower aperture components, this cable is fully compatible with multimode applications. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 50/125 multimode fiber, immune to electrical interference.

Features & Benefits

Designed to support gigabit ethernet, fibre channel, ATM, and internet protocol applications	Patented injection molding process for greater durability
Optically inspected and tested for insertion loss	Pull-proof jacket design, immune to electrical interference

Specifications

General Info

Product Line	C2G	Color	Orange
UPC Number	757120110330	Country Of Origin	Hong Kong
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	13.1 FT	Cable Length	13.1 ft
-------------------	---------	--------------	---------

Trade Programs

TAA Compliant	Yes
---------------	-----

Technical Information

Fiber Optic Cable Type	Multimode, OM2	Jacket Material	PVC (Polyvinyl Chloride)
Bend Radius	45 mm	Simplex/Duplex	Duplex
Cable Type	Fiber Optic	Jacket Rating	Standard / Non-Rated
Data Transfer Rate	10 Gbps	Connector 2	LC Male
Connector 1	LC Male	Fiber Size	50/125