

## M12 wall bracket / gender changer



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 000 0036
Specification	M12 wall bracket / gender changer
HARTING eCatalogue	<a href="https://harting.com/21010000036">https://harting.com/21010000036</a>

### Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Panel mounting parts

### Technical characteristics

Limiting temperature	-40 ... +85 °C
----------------------	----------------

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (accessories)	Thermoplastic
Colour (accessories)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

### Specifications and approvals

UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521
----------	--



**Pushing Performance**  
Since 1945

## Commercial data

Packaging size	1
Net weight	1.267 g
Country of origin	Taiwan
European customs tariff number	85389099
GTIN	5713140136533
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400