





LOC		DIST		REVISIONS			
AD		00		P	LTR	DESCRIPTION	DATE
				T		OG3C-0324-01	12OCT01
					DWN	APVD	
					RB	JO	





TYPICAL APPLICATION



SECTION J-J



SECTION K-K



RECOMMENDED PC BOARD LAYOUT
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	15OCT2001	AMP Tyco Electronics Corporation City, State, Zip					
DIMENSIONS: INCHES		CHK J OLSON	12OCT01						
		APVD J OLSON	12OCT01	NAME CONTACT, RCPT, MOD II, STRIP, SHORT POINT OF CONTACT, HORIZONTAL, TYPE 'C' ENTRY —					
		PRODUCT SPEC —							
		APPLICATION SPEC —		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL —		FINISH —		WEIGHT —		A2 00779 C-85863		—	
CUSTOMER DRAWING						SCALE	10:1	SHEET 1 OF 2	REV T

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

- 1 CONTACT LEGS SHOWN IN PHANTOM AND SHEAR LINES DEFINE LOOSE PIECE PART.
- 2 .000030 GOLD OVER .000050 NICKEL.
- 3 .000050 GOLD OVER .000050 NICKEL.
- 4 GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000030 GOLD IN CONTACT AREA ONLY.
- 5 GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000015 GOLD IN CONTACT AREA ONLY.
- 6 TIN PLATE.
- 7 POINT OF MEASUREMENT FOR PLATING THICKNESS(INSIDE OF CONTACT BEAMS).
- 8 SUPERSEDED BY 85863-4.
- 9 OBSOLETE.

9	.093	.145	2-85866-1	5	2-85863-1
9	.062	.115	1-85866-2	3	1-85863-2
8	.062	.115	1-85866-1	5	1-85863-1
9	.125	.175	1-85866-0	4	1-85863-0
9	.125	.175	85866-9	6	85863-9
9	.125	.175	85866-8	2	85863-8
9	.093	.145	85866-7	4	85863-7
9	.093	.145	85866-6	6	85863-6
9	.093	.145	85866-5	2	85863-5
	.062	.115	85866-4	4	85863-4
	.062	.115	85866-3	6	85863-3
	.062	.115	85866-2	2	85863-2
DIM B		DIM A	LOOSE PIECE PART NUMBER	FINISH	STRIP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R BROWN
15OCT01

CHK
J OLSON
12OCT01

APVD
J OLSON
12OCT01

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

DWN
R BROWN
15OCT01

CHK
J OLSON
12OCT01

APVD
J OLSON
12OCT01

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=85863

RESTRICTED TO

Tyco Electronics Corporation
City, State, Zip

CONTACT, RCPT, MOD II, STRIP, SHORT
POINT OF CONTACT, HORIZONTAL, TYPE 'C' ENTRY

SCALE
1:1

SHEET
2

OF
2

REV
T