

DETAIL B
(SCALE=5/1)



RECOMMENDED P. C. B. LAYOUT
(MOUNT SIDE VIEW)
(SCALE=5/1)





DETAIL A
(SCALE=5/1)





RECOMMENDED
PANEL CUT-OUT DIMENSIONS
(t=1.12±0.08)

NOTE 1.CONTACT PLATING
CONTACT AREA:GOLD 0.1 μm MIN. OVER PALLADIUM/NICKEL 0.5μm
TERMINAL AREA:GOLD 0.05 μm
ALL OVER NICKEL UNDERPLATED.
2.TWO LOCK SCREWS(ITEM #5) ARE SUPPLIED WITH CONNECTOR.

No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
6	HOLD DOWN	PHOSPHOR BRONZE	2	NICKEL	M2x0.4
5	LOCK SCREW	STEEL	2	NICKEL	M2
4	SHELL	STEEL	1	NICKEL	———
3	INSULATOR	PA9T	1	———	UL94V-0 BLACK
2	CONTACT	PHOSPHOR BRONZE	68	SEE NOTE 1	———
1	BRACKET	PPS	1	———	UL94V-0 BLACK

LTR.	DATE	BY	REV. DESCRIPT
3			
2			
1			

DATE	SCALE	UNIT	3RD. A. P
Jun.10.2004	2 / 1	mm (INCH)	
APP. DATE&REV.			

DR.	DE.	CHK.	CHK.	APP.
Y.KATO	Y.KATO	—	C.NUNOKAWA	H.EBIHARA

HONDA TSUSHIN KOGYO CO., LTD.

NAME	0.8mm SPACING 68POS. R/A FEMALE CONNECTOR (ONE MOLD TYPE)	
PART NO.	HDRA-EC68LFDT-SL+	REV.

ID= HDRA-EC68LFDT-SL+ E0

Downloaded from Arrow.com.