
Part Number : 554451029
Product Description : 2.00mm Pitch I/O PCB Receptacle, Upright-Style, Phosphor Bronze Shell, 10 Circuits
Series Number : 55445
Status : Active
Product Category : I/O Connectors



Documents and Resources

Drawings

554451029_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

554459200-200.pdf

554450000-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	55445
Description	2.00mm Pitch I/O PCB Receptacle, Upright-Style, Phosphor Bronze Shell, 10 Circuits
Application	Wire-to-Board
Component Type	Receptacle
Product Name	2.00mm I/O Connectors
Type	N/A
UPC	191128174824

Agency

UL	E29179

Electrical

Current - Maximum per Contact	2.0A
Shielded	Yes
Voltage - Maximum	125V

Physical

Circuits (Loaded)	10

Downloaded from Arrow.com.

Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6139.148/mg
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.00mm
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.305µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.00mm Pitch I/O Hand Soldering Type Plug Set, Black Cover, 10 Circuits	545991016
2.00mm Pitch I/O Hand Soldering Type Plug Set, Gray Cover, 10 Circuits	545991019

Downloaded from Arrow.com.

2.00mm Pitch I/O Hand Soldering Type Plug Set, Black Cover, 10 Circuits	545991026

This document was generated on Jun 02, 2026

Downloaded from Arrow.com.