

Specifications



Photo is representative



Eaton E34VFBK1-1X

Eaton E34 pushbutton, E34 series pushbuttons and indicating lights, 30.5 mm, Corrosion Resistant, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Knob, Black actuator, 1NO-1NC_assembled

General specifications

PRODUCT NAME	Eaton E34 pushbutton
CATALOG NUMBER	E34VFBK1-1X
UPC	782113880334
PRODUCT LENGTH/DEPTH	3.25 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.34 lb
WARRANTY	1 year
COMPLIANCES	FDA 3-A CE Marked
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Assembled at Factory

Product specifications

TYPE	30.5 mm, Corrosion Resistant
ACTUATOR COLOR	Black
CAM CODE	Cam 1
ACTUATOR	Knob
CONTACT CONFIGURATION	1 NO-1 NC
ILLUMINATION	Non-illuminated
NEMA RATING	NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13
RATING	NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13
SERIES	E34
NUMBER OF POSITIONS	2
THROW TYPE	60 °

Resources

MULTIMEDIA

[How to size and select a Power Supply](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - E34VFBK1-1X](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

