



Part Number : [2064600023](#)

Product Description : Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 24-20 AWG

Series Number : 206460

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[2064600023_sd.pdf](#)

[2064600000-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2064600001-AS-000.pdf](#)

[2064600000-PS-000.pdf](#)


[2159530000-PS-000.pdf](#)

[2064600000-TS-000.pdf](#)

[2064600001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	206460
Description	Micro-Fit+ Crimp Terminal, Female, 0.75µm Gold (Au) Plating, 24-20 AWG
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Fit+
UPC	193264161881

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	9.8A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Durability (mating cycles max)	200
Gender	Female

Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	0.066/g
Packaging Type	Reel
Plating min - Mating	0.760µm
Plating min - Termination	1.520µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.85mm
Wire Size (AWG)	20, 22, 24
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Receptacle Housings	<u>206461</u>
Micro-Fit+ Single Row Receptacle Housings	<u>215759</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>11030043</u>
FineAdjust Applicator for Micro-Fit+ Crimp Terminals, 24-20 AWG, Insulation OD 0.90-1.10mm	<u>2037023500</u>
FineAdjust Applicator for Micro-Fit+ Crimp Terminals, 24-20 AWG, Insulation OD 1.11-1.30mm	<u>2037023600</u>
FineAdjust Applicator for Micro-Fit+ Crimp Terminals, 24-20 AWG, Insulation OD 1.31-1.85mm	<u>2037023700</u>

Hand Crimp Tool for Micro-Fit Crimp Terminals, 20 AWG, UL1007 and UL1061 Wires	<u>2133094500</u>
Hand Crimp Tool for Micro-Fit Crimp Terminals, 22 AWG, UL1007 and UL1061 Wires	<u>2133094600</u>
Hand Crimp Tool for Micro-Fit+ Crimp Terminals, 24 AWG, UL 1007 and UL 1061 Wires	<u>2133094700</u>
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 30-20 AWG	<u>638120800</u>

This document was generated on Dec 11, 2025