


Part Number : [1301120246](#)
Product Description : Guard Only (LITE-A-SITE),
Polypropylene
Series Number : 130112
Status : Active
Product Category : Portable Lighting Accessories
Engineering Part Number : STR101



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Portable Lighting Accessories
Series	130112
Description	Guard Only (LITE-A-SITE), Polypropylene
NEMA Configuration	N/A
Product Name	Woodhead
Type	Accessory
UPC	78678879982

Electrical

Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	109.22mm (4.300")
Duty	Commercial
Guard Included	Yes
Guard Type	Polypropylene
Height	165.10mm (6.500")
Lamp Type	A21
Length	N/A
Material - Guard	Polypropylene
Net Weight	45.359/g
Outlet	None
Packaging Type	Carton

This document was generated on May 19, 2026