Specification Sheet

Part Number: 126-02300



An all-in-one bundling and fixing solution reduces costs.

Disc provides secure insertion and minimizes access of dust, dirt and water.

1-Piece Cable Tie with Arrowhead Mount, 7.0"L, 50lb Tensile, PA66HIRHS, Natural, 1000/pkg

Article Number	126-02300
Type	T50SST5
Color	Natural (NA)
Quantity Per	pack
Product Description	The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to kieep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
Short Description	1-Piece Cable Tie with Arrowhead Mount, 7.0"L, 50lb Tensile, PA66HIRHS, Natural, 1000/pkg
Global Part Name	T50SST5-PA66-NA

Downloaded from Arrow.com.

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	7.0
Length L (Metric)	170.0
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.22
Bundle Diameter Max (Metric)	31.0
Thickness T (Imperial)	0.05

Downloaded from Arrow.com.

Thickness T (Metric)	1.2
Height H (Imperial)	0.4
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.06
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	1.5
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 "
Mounting Hole Diameter D (Metric)	6.1 - 6.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.5
Disc Diameter (Metric)	16.2
Disc Diameter (Imperial)	0.64

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Downloaded from Arrow.com.

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.