



## Johanson Product Information for 2450AT18B0100001E

**Johanson Company: Johanson Technology inc.**

Termination: Ni/Sn (RoHS)

Deprecated P/N: 2450AT18B100E

Marking: Orientation Mark

Datasheet Date: 08-13-2022

Product Release Date: 07 June, 2007

Description: Antennas, 1206, 2400-2500MHz, 2W, 0.5dBi (typ), Ni/Sn (RoHS), 7" Reel Embossed Tape

Web Page Link:

<https://www.johansontechnology.com/antennas>

Life Cycle Stage: Active - Production

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.055

Schedule B: 8529.10.60.00

Thickness (Min): 0.043

Harmonization Code: 8529.10.60.00

End Band (Min): 0.008

ITAR: No

End Band (Max): 0.032

ECCN: EAR99

Standard Item: Yes

RoHS Compliance: Yes, RoHS 10/10

Lead Time Typical (Weeks)\*:

\*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 14

REACH: Yes

Country of Origin: TW

Length (Min): 0.114

Product Family: Antennas

Length (Max): 0.138

Product Subfamily: Antennas

Width (Min): 0.051

Width (Max): 0.075