


© 2021 TE Connectivity. All Rights Reserved.



RECOMMEND PANEL HOLE



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP ECN-22-148830	22APR2022	JZ	WKH
	A1	ECR-22-141436	07JUN2022	JZ	WKH
	A2	ECR-22-146298	15JUL2022	JZ	WKH



1-2404600-0	1000±10
2404600-9	750±5
2404600-8	500±5
2404600-7	350±5
2404600-6	300±3
2404600-5	250±3
2404600-4	200±3
2404600-3	150±3
2404600-2	100±3
2404600-1	50+3
P/N	LENGTH

NOTES:
1. MATERIAL AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702
2. PRODUCT RATING:
   CHARACTERISTIC IMPEDANCE: 50 OHMS Normal
   FREQUENCY RANGE: DC TO 9GHz
3. CABLE ASSEMBLY TO BE 100% OPEN,SHORT
4. SMA BODY,CC,WASHER,NUT ARE GOLD PLATING
5. UMCC GEN1 CAN MATE WITH I-PEX MHF SERIES AND HIROSE U.FL SERIES

PC	HEAT SHRINK TUBE, BLACK	4
LENGTH	COAX CABLE 1.13MM BLACK	3
1PC	UMCC GEN1, IPEX 20278-112R-13 OR EQUIVALENT	2
1PC	SMA BULKHEAD JACK WITH O-RING	1
QTY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
-

FINISH -
-

DWN JZ 03DEC2021
CHK WKH 03DEC2021
APVD - -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME
RF CA, UMCC GEN1 TO SMA BH JACK
WITH 1.13MM CABLE
WITH O-RING, IP67 FOR SMA FLANGE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2404600	-


CUSTOMER DRAWING


SCALE 1:1 SHEET 1 OF 2 REV A2

Downloaded from Arrow.com.

© 2021 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





NOTES :

1. DIMENSION:

   CARTON: L=320, W=300, H=180

2. QUANTITY:

   2.1 PRIMARY PACKING: 10 PCS/BAG(10PCS)

   2.2 SECONDARY PACKING: 10 BAG/BIG BAG(100PCS)

   2.3 OUTER PACKING: 5 BIG BAG/CARTON(500PCS)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-
MATERIAL - -	FINISH - -

DWN JZ	03DEC2021
CHK WKH	03DEC2021
APVD -	-
PRODUCT SPEC -	
APPLICATION SPEC -	
WEIGHT -	

TE Connectivity

NAME
RF CA, UMCC GEN1 TO SMA BH JACK
WITH 1.13MM CABLE
WITH O-RING, IP67 FOR SMA FLANGE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2404600	-

CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 2	REV A2

Downloaded from Arrow.com.