




Part Number : [1201089135](#)
Product Description : Micro-Change (M12) Double-Ended Cordset, 8-Pole X-Coded Male (Straight) to 4-Pole D-Coded Male (Straight), 24 AWG, Teal TPE Cable, 42.0m (137.80') Length
Series Number : 120108
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : E12A06004M420



Documents & Resources

Drawings

[1201089135_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead; 6,6'-Di-tert-butyl-2,2'-methylenedi-p-cresol per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120108
Description	Micro-Change (M12) Double-Ended Cordset, 8-Pole X-Coded Male (Straight) to 4-Pole D-Coded Male (Straight), 24 AWG, Teal TPE Cable, 42.0m (137.80') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	196823084171

Agency

UL	E361772
----	---------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	48V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	42.0m (137.80')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)

Coupling Style	Threaded
Gender	Male-Male
Keyway	D-Coded, X-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	1833.680/g
Orientation	Straight to Straight
Poles	4, 8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	Unshielded TPE/AWM 2463
Wire Size (AWG)	24

This document was generated on Sep 11, 2025