

Part Number : [1300980122](#)

Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male with O-Ring, Cable Diameter 15.88-19.05mm (.625-.750"), Polyester



Series Number : 130098

Status : Active

Product Category : Cable Grips

Engineering Number : 5542WBLK

Documents & Resources

Drawings

[1300980122_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male with O-Ring, Cable Diameter 15.88-19.05mm (.625-.750"), Polyester
NEMA Rating	NEMA 6P
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855423

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	Orange
Eye Type	N/A
Gender	Male
Material - Body	PBT
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	Yes
Thread Size	3/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>

This document was generated on Sep 18, 2025