Part Number : 192030379
Product Description : Krimptite Quick Disconnect, Female, Steel, 483°C (900° F), 12-10 AWG, Tab 6.35mm, Carton
Series Number : 19203
Status : Active
Product Category : Quick Disconnects



Documents and Resources

Drawings

192030379_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19203
Description	Krimptite Quick Disconnect, Female, Steel, 483°C (900° F), 12-10 AWG, Tab 6.35mm, Carton
Product Name	Krimptite
Type	Standard Quick Disconnect
UPC	822348424689

Electrical

Voltage - Maximum	N/A

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	No
Material - Metal	Steel
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	0.670/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	1.270µm

Downloaded from Arrow.com.

Plating min - Termination	1.270µm
Tab Thickness	0.80mm
Tab Width	7.70mm
Temperature Range - Operating	483°C
Wire Size (AWG)	10, 12

Application Tooling

Global

Description	Part Number
Hand Tool for High Temperature Female Quick Disconnects	640031500

Downloaded from Arrow.com.