









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECN-25-313805	27MAR2025	TR	NSK

- NOTES :
- MATERIAL:
HOUSING: THERMOPLASTIC, UL 94V-0, COLOR: SEE TABLE.
CONTACT: PHOSPHOR BRONZE, THICKNESS=0.25mm.
SHELL: STAINLESS STEEL, THICKNESS=0.30mm.
 - FINISH:
CONTACT: GOLD FLASH OVER 0.762um [30u"] MIN. PALLADIUM-NICKEL OR ALTERNATIVE 0.762um [30u"] MIN. GOLD PLATING ON CONTACT AREA,
2.54um [100u"] MIN. MATTE-TIN PLATING ON SOLDER TAILS,
1.27um [50u"] MIN. NICKEL UNDERPLATED OVER ALL.
ⓔ SHELL: 2.54um [100u"] MIN. NICKEL PLATED OVER
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.
- ⚠ PRELIMINARY PART.
- ⚠ CUSTOMER RESTRICTED PART, NOT FOR GENERAL SALES.



ⓔ	BLACK	1734517-5
ⓔ	BLUE	1734517-4
	WHITE	1734517-3
	BLACK	1734517-1
	H/S COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	20MAR2019		<div>TE Connectivity Ltd.</div>						
		CHK S.LI	21MAR2019								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME USB B TYPE, TOP ENTRY, 4 POSITION, SMT TYPE —						
		APVD S.LI							21MAR2019		
		PRODUCT SPEC 108-57538									
		APPLICATION SPEC —									
MATERIAL —		FINISH —			SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
		WEIGHT —			A3	00779	C-1734517		—		
CUSTOMER DRAWING					SCALE	N/A		SHEET	1 of 3	REV	E

