
Part Number : 2250190050
Product Description : Easy-On FlexiSnap-15 FFC/FPC Connector, 0.50mm Pitch, 1.50mm Height, Dual Contact Style, Right-Angle, Surface Mount, 5 Circuits, Gold Plating
Series Number : 225019
Status : Active
Product Category : FFC / FPC Connectors



Documents and Resources

Drawings

2250190050_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

2250190050.dxf

Specifications

2250199200-SPK-200.pdf

2250190000-AS-EN.pdf

2250190000-AS-JP.pdf

2250190000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	FlexiSnap-15
Description	Easy-On FlexiSnap-15 FFC/FPC Connector, 0.50mm Pitch, 1.50mm Height, Dual Contact Style, Right-Angle, Surface Mount, 5 Circuits, Gold Plating
Product Name	Easy-On
UPC	198282876984

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	One-Touch
Circuits (Loaded)	5
Color - Resin	Black
Contact Position	Dual

Downloaded from Arrow.com.

Durability (mating cycles max)	20
Mated Height	1.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	108.533/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	No
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.50mm Pitch Premo-Flex FFC Jumpers	15036

Downloaded from Arrow.com.