

ASSMANN
components

deutsch | english

Search:



The company | **Products** | Articlefinder | Contacts | Distribution | Download | Service

Connectors

- Customer specific solutions
- D SUB
- D SUB cover
- D SUB accessories
- DVI
- Centronics
- IDC
- Modular
- USB
- IEEE 1394
- Switches
- Power supply
- DIN 41612
- DIN 41617
- Mini DIN
- IC Socket
- **Pin and female header**
- Jumper
- Connector sleeves
- Solder terminals
- Test terminals
- Terminal Blocks
- Memory Card connectors
- FFC / FPC connectors
- Micro-Miniature



Pin and female header

AW 109/06-T
female-header 16pins THT 2,54mm 3A single row 25,90mm straight Sn

Article number: AW 126 16 Z T

product group: pin-&female-header

style: female-header

contact type: THT

pin count: 16

spacing in mm: 2,54

current rating: 3A

version: single row

contact length: 25,90mm

contact direction: straight

plating: Sn

contact machining: turned contacts

packaging: polybag

process: THT

insulator: PBT UL94V-0

: AW 109/06-T

: #NV

» PDF download «

Thermal management

Cable assembly



