

MT53E384M32D2DS-O46 AUT:E

Documents

<div><div></div>Reach Statement</div>
<div><div>Reach Statement</div><div>REACH: Registration, Evaluation, Authorization, and Restriction of Chemicals File Type: pdf Updated: 2024-12-27</div><div>Download</div></div>
<div><div></div>Sim Model</div>

Specifications

Component Density 12Gb	Speed 2133MHz	MT/s 4266MTPS	I/O Voltage 1.1/0.6 VOLTS	Operating Temp -40C to +125C	Bus Width x32
CAS Latency CL = Programmable	Pin Count 200-ball	Part Status Code Obsolete	Component Config 384M x32	Dry Pack Qty 1360	Package Dimension (W x L x H) mm 10.00 x 14.50 x 0.80
Tape & Reel Qty 2000	Package Type GREEN	Number of Components 2	Package WFBGA	Family DRAM	Technology LPDDR4