



Circuit Board Indicators
Panel Mount Indicators
Solid State Lighting
Traffic Signals
Vehicle Lighting
Rail
Obstruction Lighting
Hazardous Area Lighting
Heliport Lighting

how to purchase

sales contacts

stock check

search

Product Line Search
Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:
Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# 5530213200F
3 mm Lens

Description
Package Options
Product Type
Sub Product Type
Configuration
Viewing
Viewing Angle
Test Current (mA)

3 mm Bi-Level CBI
50 Pieces Per Bag
Through Hole Indicators with Bi-Level Housing
3 mm Lens
Right Angle
60
2mA

Absolute Maximum Ratings
(Ta = 25 °)

Solder Temp
Operating Temp
Storage Temp

260Â° for 5 sec
-55 to +100° C
-55 to +100° C

RoHS /pB Free
view PDF

Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2
Color	Red	Green
Lamp Type	Single Color	Single Color
LED Type	Low Current	Low Current
Intensity Min (mcd)	1.0	1.0
Intensity Typ (mcd)	1.6	1.6
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)	20	20
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.
5530213200F

check stock



Copyright 2006 Dialight. All rights reserved | [Privacy Policy](#)

Downloaded from [Arrow.com](#)