



Representative Image

**Catalog No. GSB550****Description: TWO-PIECE INNER SLV CONN BLUE RND****UPC No 786210813301****Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Two Piece Inner Sleeve Connector for Round Range, Length 11.2mm, Inner Diameter 13.97mm, Outer Diameter 15.75mm, Copper Alloy, Color Blue, Tin Plated

**Descriptors**

Category	Electrical terminals
Special Features	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Circular Range (the corresponding outer sleeve is crimped with a hydraulic head and the result is a circular-shaped crimp), for grounding multiple or overall shielded cables. The sleeves are color coded according to their size. Applications in communications, aerospace, and electronics.

**Specifications**

Material	Copper
Color	Blue

**Classifications**

Brand Name	Sta-Kon
Sub Brand	Shield-Kon

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC002650 Connection for screened wires
Model	2-part
Sleeve form	Internal sleeve
Insulated	N
Outer diameter sleeve	15.75 mm
Inner diameter sleeve	13.97 mm
Sleeve length	15.2 mm
Sleeve length	0.6 inch

by ABB

ETIM	EC002650 Connection for screened wires
Colour code	Blue
Compression shape	Round
Reel packaging	N