YSV14H, Uninsulated Splice For 16 - 14 AWG



By Burndy
Catalog # YSV14H

Uninsulated Splice with Cable Strain Relief, 16-14 AWG, Seamless Butt Splice, Electrolytic Copper Tubing, Tin Plated, Wire Stops, Bulk Package

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper depth of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Navy Size Range	2 1/2 (1)-4 (41)
Conductor - Copper Str Navy Size	• 2 1/2 (1) • 2 1/2 (19) • 2 1/2 (26) • 3 (7) • 4 (1) • 4 (7) • 4 (19) • 4 (41)
Conductor - Copper Solid Size	12
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Aircraft Size	• AN 20 • AN 18 • AN 16 • AN 14
Conductor - Copper Solid Size Range	12
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor - Copper Str Size	• 20 • 18 • 16 • 14

Configuration

Connector Type	Seamless Butt Splice

Current

Voltage - Maximum	35000 V

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	24 mm
Dimension - B Length inch	0.24 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Inside Diameter inch	0.09 in
Dimension - Length Overall inch	0.94 in
Dimension - Strip Length inch	1/4

General

Feature - Barrel Style	Shrouded
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYLINK™
Product Type	Splice
UPC	781810805718
Type	Splice
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810805718
UPC 14 Digit GTIN	00781810805718

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	1000

Operational

Downloaded from Arrow.com.

Temperature Rating	90

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.