

KNAC0401ASM - Asymmetric For Residential & Industrial Light



- Material = PMMA
- Full angle at 50% from maximum: $\sim 135^\circ \times 101^\circ$
- Full angle at 10% from maximum: $\sim 167^\circ \times 164^\circ$
- The light spots here represented refer to tests carried out with LEDs with 3mm dome, $\sim 250\text{lm}$

