Part Number : 430251208
Product Description : Micro-Fit 3.0 Receptacle Housing, Dual Row, 12 Circuits, UL 94V-0, Low-Halogen Since Inception, Black
Series Number : 43025
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

430251208_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

430250000-AS-000.pdf

430450001-AS-000.pdf

PK-43025-001-001.pdf

430450001-PS-KO-000.pdf

430450001-PS-SP-000.pdf

PS-43045-001.pdf

430450005-TS-000.pdf

430450007-TS-000.pdf

TS-43045-001-001.pdf

TS-43045-003-001.pdf

TS-46235-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	43025
Description	Micro-Fit 3.0 Receptacle Housing, Dual Row, 12 Circuits, UL 94V-0, Low-Halogen Since Inception, Black
Application	Wire-to-Board, Wire-to-Wire
Comments	Halogen Free/Low Halogen since inception
Component Type	Receptacle
Product Name	Micro-Fit 3.0
UPC	883906102180

Agency

CSA	LR19980
UL	E29179

Downloaded from Arrow.com.

Physical

Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.691/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Plug Housings	43020
Micro-Fit 3.0 Dual Row Headers	43045
Micro-Fit 3.0 Dual Row Test Plugs	44242

Use with Part(s)

Description	Part Number
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Tin (Sn) Plating, 150.00mm Length, 20 AWG, Black	797580002
Pre-Crimped Lead Micro-Fit 3.0	797580004

Downloaded from Arrow.com.

Female-to-Micro-Fit 3.0 Female, Gold (Au) Plating, 150.00mm Length, 20 AWG, Black	
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Tin (Sn) Plating, 300.00mm Length, 20 AWG, Black	797580010
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Gold (Au) Plating, 300.00mm Length, 20 AWG, Black	797580012
Micro-Fit 3.0 Female Crimp Terminals	43030
Micro-Fit 3.0 Female Crimp Terminals with Lubricant	45773
Micro-Fit Reduced Mating Force Female Crimp Terminals	46235
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female	214760
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Pigtail	214761

Downloaded from Arrow.com.