Specifications



Photo is representative





Eaton SD8328-101-R

Eaton SD8328 inductor, 97 uH, 0.8 A Irms, 0.8 A ISAT, 430 mΩ resistance, SMT mounting, Ferrite, 2-pins, 1280 qty.

General specifications	
PRODUCT NAME	Eaton SD8328 inductor
CATALOG NUMBER	SD8328-101-R
UPC	051712826204
PRODUCT LENGTH/DEPTH	9.5 mm
PRODUCT HEIGHT	3 mm
PRODUCT WIDTH	8.3 mm
PRODUCT WEIGHT	0.629 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.8 A
ISAT	0.8 A
PACKAGE QUANTITY	1280
MATERIAL	Ferrite
FREQUENCY RATING	Up to 1 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	430 mΩ
SERIES	SD8328

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SD8328-101-R
TECHNICAL DATA SHEETS	SD8328 Low profile shielded drum core power inductors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.

Downloaded from Arrow.com.