
Part Number : 982670754
Product Description : 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 152.00mm Cable Length, Tin (Sn) Plating, 7 Circuits
Series Number : 98267
Status : Active
Product Category : Flat-Flexible Cable (FFC)



Documents and Resources

Drawings

982670754_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-98267-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	98267
Description	1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 152.00mm Cable Length, Tin (Sn) Plating, 7 Circuits
Comments	Contacts on opposite sides, Type D
Product Name	Premo-Flex FFC Jumper
UPC	800756947341

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

Physical

Cable Length	152.00mm
Circuits (Loaded)	7
Contact Layout Type	D (opposite side)
Design Feature	Extra-Flexible
Material - Plating Mating	Tin
Net Weight	0.983/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector
Wire/Cable Type	Flat Flexible Cable (FFC)

Downloaded from Arrow.com.

Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Bottom Contact, 3.00mm Height, 7 Circuits, Tin-Bismuth Plating	522710779
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 7 Circuits, Tin-Bismuth Plating	526100771
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 7 Circuits, Tin-Bismuth Plating, with Pick-and-Place Tape	526100775
Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, 7 Circuits	528080770
Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, with Pick-and-Place Polyimide Tape, 7 Circuits	528080771
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 7 Circuits, Tin-Bismuth Plating	522070785
Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Right-Angle, Non-ZIF, Top Contact Style, 7 Circuits	527930770
1.00mm Pitch Easy-On FFC/FPC Connector, Vertical, Surface Mount Compatible, Non-ZIF,	528060710

Downloaded from Arrow.com.

Kinked PC Tails, 7 Circuits	
1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 7 Circuits	528070710
Easy-On FFC/FPC Connector, 1.00mm Pitch, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 7 Circuits	528520770

Downloaded from Arrow.com.