Your Expert Partner for **Human Machine Interfaces**

Actuator

45-
2T07.4FH0.000



https://www.eao.com/component/45-2T07.4FH0.00...

Downloaded from Arrow.com.

Your product:



45-2T07.4FH0.000
Actuator

FRONT

Front dimension:	Ø 38 mm
Front form:	Round
Front bezel colour:	Sand grey
Front bezel material:	Metal

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens cap colour:	Green
Lens cap material:	Plastic
Lens cap shape:	flush
Lens cap optical effect:	transparent
Illumination colour:	Green

MECHANICAL CHARACTERISTICS

Weight:	0.08 kg

AMBIENT CONDITION

IP front protection:	IP66, IP67, IP69K

Downloaded from Arrow.com.

Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 80 °C
Shock resistance:	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms
Vibration resistance:	According to IEC 60068-2-6: 2 ... 500 Hz: 5 g
Climate resistance:	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6


CERTIFICATE

REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER


Short Description:	Actuator, Ø 22.3 mm, Ø 38 mm, Round, Sand grey, Metal, IP66, IP67, IP69K, Green
Housing material:	Metal
Hints:	Front panel thickness 1 ... 6 mm

Wiring diagrams:



Dimension drawings:

Downloaded from Arrow.com.



Downloaded from Arrow.com.