

# Product data sheet

Specifications



## Line-R 1200VA Automatic Voltage Regulator

LE1200

 To be discontinued on: Aug 6, 2024

 To be discontinued

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Main Input Voltage	120 V
product or component type	Uninterruptible power supply (UPS)
Main Output Voltage	120 V
Rated power in W	1200 W
Rated power in VA	1200 VA
Input Connection Type	NEMA 5-15P
Cable length	2.0 m
Number of cables	1
Provided equipment	User manual

### Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0

### Physical

Colour	Beige
Height	11.6 cm
Width	21.4 cm
Depth	14.1 cm
net weight	4.4 kg
Mounting preference	No preference
mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

### Input

Network frequency	50/60 Hz
-------------------	----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Output

Maximum configurable power in W	1200 W
---------------------------------	--------

## Conformance

Product certifications	cUL listed NOM
Standards	FCC part 15 class B UL 1012
Equipment protection policy	Lifetime : \$25000

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.0000000000...15240.0000000000 m

## Surge Protection and Filtering

Surge energy rate	680 J
-------------------	-------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.5 cm
Package 1 Width	20.7 cm
Package 1 Length	27.3 cm
Package 1 Weight	4.7 kg
SCC14	10731304197918

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>