
Part Number : 354076702
Product Description : 2.28mm Sealed Terminal, Female, 0.30-0.50mm² AVSS, 0.25mm Material Thickness, Pre-Tin Plated
Series Number : 35407
Status : Obsolete
Product Category : Crimp Terminals



Obsolete

Documents and Resources

Drawings

354076702_sd.pdf

Specifications

PK-35407-003-001.pdf

PS-35408-001-001.pdf

Tooling Specifications

CS-35407-6702-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	35407
Description	2.28mm Sealed Terminal, Female, 0.30-0.50mm² AVSS, 0.25mm Material Thickness, Pre-Tin Plated
Application	Wire-to-Board
Product Name	N/A
UPC	800756627809

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.293/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size (AWG)	20, 22
Wire Size mm²	N/A

Mates With / Use With

Mates with Part(s)

Obsolete

Downloaded from Arrow.com.

Description	Part Number
Tab Terminals	35420

Use with Part(s)

Description	Part Number
Automotive Horn Female Housings	35825

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for 2.28mm (.090") Sealed Receptacle Terminals	638257600

This document was generated on Sep 16, 2026

Obsolete

Downloaded from Arrow.com.