

PushPull SFP XS Receptacle short, LC Dup



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 411 0501 200
Specification	PushPull SFP XS Receptacle short, LC Dup
HARTING eCatalogue	https://harting.com/09574110501200

Identification

Category	Connectors
Series	PushPull XS SFP
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Short version Only for LC transceiver

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥50
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Commercial data

Packaging size	50
Net weight	6.3 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140224070
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466